

# List of part numbers



Part number	Page	Part number	Page	Part number	Page	Part number	Page
09 47 800 0002	B1.91	20 10 001 5217	B1.41	20 76 105 3000	A1.08	20 79 302 0922	B1.74
09 47 800 0003	B1.91	20 10 001 5217	B1.43	20 76 105 3001	A1.10	20 79 302 0922	B2.66
09 47 800 0005	B1.91	20 10 001 5217	B1.55				
09 47 800 0006	B1.91	20 10 001 5217	B1.57				
09 47 800 0011	B1.91			20 76 107 3100	A1.21		
09 47 800 0013	B1.91			20 76 107 3200	A1.25	20 80 000 0003	A1.47
09 47 800 0022	B1.91	20 10 125 5211	B1.41			20 80 000 0003	A4.43
		20 10 125 5211	B1.43			20 80 000 0003	B3.19
		20 10 125 5211	B1.55	20 76 108 3000	A1.17	20 80 000 0007	A6.06
		20 10 125 5211	B1.57	20 76 108 3001	A1.18		
09 47 808 0002	B1.90			20 76 108 3002	A1.19		
09 47 808 0003	B1.90			20 76 108 3004	A1.20	20 80 010 0001	A1.47
09 47 808 0005	B1.90	20 10 230 5211	B1.41	20 76 108 3100	A1.22	20 80 010 0001	A4.43
09 47 808 0006	B1.90	20 10 230 5211	B1.43	20 76 108 3102	A1.23	20 80 010 0002	A1.47
09 47 808 0011	B1.90	20 10 230 5211	B1.55	20 76 108 3103	A1.24	20 80 010 0002	A4.43
09 47 808 0013	B1.90	20 10 230 5211	B1.57				
09 47 808 0022	B1.90			20 76 108 3200	A1.26		
				20 76 108 4000	A4.14	20 80 024 0002	A1.47
						20 80 024 0002	A4.43
09 47 900 0001	B2.19	20 16 111 2110	A4.47				
		20 16 111 3110	A4.47	20 76 109 1100	A2.09	20 80 300 3025	A5.05
		20 16 111 4110	A4.47	20 76 109 4101	A4.21	20 80 300 3026	A5.03
				20 76 109 4201	A4.24	20 80 300 3027	A5.04
09 57 402 0500 000	B2.29						
09 57 402 0501 000	B2.29						
		20 70 305 3923	A1.42	20 76 110 1000	A2.07		
09 57 441 0500 000	B2.29	20 70 305 3943	A1.43	20 76 110 1001	A2.08	20 82 000 0001	B3.07
09 57 441 0501 000	B2.29	20 70 305 4943	A4.39	20 76 110 1100	A2.10	20 82 000 0001	B3.09
				20 76 110 1100	A2.10	20 82 000 0002	B3.07
				20 76 110 4002	A4.19	20 82 000 0003	B3.07
09 57 442 0502 001	B2.29	20 70 310 3924	A1.45	20 76 110 4003	A4.20	20 82 000 9901	B3.26
09 57 442 0503 001	B2.29	20 70 310 3942	A1.44	20 76 110 4101	A4.22	20 82 000 9915	B3.26
		20 70 310 4924	A4.41	20 76 110 4102	A4.23	20 82 000 9916	B1.11
		20 70 310 4945	A4.40	20 76 110 4201	A4.25	20 82 000 9916	B2.13
						20 82 000 9916	B3.26
09 99 000 0382	B1.106						
09 99 000 0501	B2.79	20 76 000 0300	A6.03	20 76 112 4300	A4.15	20 82 001 0001	B1.49
09 99 000 0525	B2.79					20 82 001 0001	B1.52
		20 76 010 0300	A6.04	20 76 116 3000	A1.09	20 82 001 0001	B2.47
						20 82 001 0001	B2.49
		20 76 020 0300	A6.03	20 76 207 7000	A1.37	20 82 001 0001	B3.07
				20 76 207 7002	A4.34	20 82 001 0002	B3.07
10 12 005 1002	B1.83						
10 12 005 1002	B2.75	20 76 024 0300	A6.03			20 82 101 0220	B3.19
10 12 005 2001	B1.79						
		20 76 028 0300	A6.03	20 76 208 7002	A4.35	20 82 102 0101	B3.22
				20 76 208 7003	A1.38		
		20 76 030 0300	A6.04			20 82 104 0101	B3.23
				20 77 208 3001	A1.32		
19 00 000 5020	B3.26	20 76 034 0300	A6.04	20 77 208 3003	A1.33	20 82 400 0001	B3.15
19 00 000 5070	C2.12			20 77 208 3009	A1.34		
19 00 000 5071	C2.12					20 82 405 0001	B3.17
19 00 000 5072	C2.12	20 76 038 0300	A6.04	20 77 208 4001	A4.29		
19 00 000 5079	B3.26			20 77 208 4003	A4.30		
19 00 000 5080	A1.46			20 77 208 4009	A4.31	20 82 500 0001	B3.09
19 00 000 5080	A4.42	20 76 102 3100	A1.27				
19 00 000 5082	C2.12	20 76 102 3101	A1.28				
19 00 000 5090	C2.12	20 76 102 8000	B1.22			20 82 501 0001	B3.09
19 00 000 5094	C2.12	20 76 102 8000	B2.21	20 78 106 4000	A3.13		
		20 76 103 3000	A1.06			20 82 600 1002	B3.10
				20 78 110 1000	A3.07	20 82 600 1004	B3.10
19 20 003 1440	A1.46			20 78 110 4000	A3.14	20 82 600 1006	B3.10
19 20 003 1440	A4.42	20 76 104 3000	A1.07	20 78 110 4300	A3.15	20 82 600 1008	B3.10
						20 82 600 1010	B3.10