



DIN 41612 Complementary type M-flat female connectors

Identification	Number of contacts	Contact arrangement	Part number	Performance levels according to IEC 60 603-2	
			3	2	1
Female connector with press-in terminations 4.5 mm	24 + 8		Performance level 3 on request	09 03 224 6830	Performance level 1 on request

Dimensions

Order high current contacts separately, see page 00.44

Panel cut out

Board drillings
Mounting side

Pre-loaded with special contacts on request
Further types see DIN 41612 catalogue

Dimensions in mm