



Male connectors straight, with press-in termination

Identification	Number of contacts	Contact length [mm] mating side	termination side	Part number	Contact configuration
Connectors with flange without coding without endwall	72	8.2	3.7	17 43 072 1209 17 43 072 2209	
	144	8.2	3.7	17 46 144 1207 17 46 144 2207	
Connectors with flange with coding 1 without endwall	72	8.2	3.7	17 43 072 1211 17 43 072 2211	
	144	8.2	3.7	17 46 144 1209 17 46 144 2209	
Connectors with flange with coding 2 without endwall	72	8.2	3.7	17 43 072 1210 17 43 072 2210	
	144	8.2	3.7	17 46 144 1208 17 46 144 2208	
Connectors with flange with coding 3 (= coding 1 + 2) without endwall	72	8.2	3.7	17 43 072 1212 17 43 072 2212	
	144	8.2	3.7	17 46 144 1210 17 46 144 2210	

Connector dimensions see pages 02.06 and 02.07.
The pin types A, B, C ... R, S, T can be mixed in any configuration.
Please request the part number.

Thin print part numbers: performance level 1
Bold print part numbers: performance level 2