



Female connectors angled, with press-in termination

harbus[®] HM 6-row

Identification	Number of contacts	Contact length [mm] termination side	Part number
Connectors without flange without coding	72	3.35	17 51 072 1102 17 51 072 2102
	144	3.35	17 54 144 1102 17 54 144 2102
Connectors with flange without coding	72	3.35	17 52 072 1105 17 52 072 2105
	144	3.35	17 55 144 1105 17 55 144 2105
Connectors with flange with coding 1	72	3.35	17 52 072 1106 17 52 072 2106
	144	3.35	17 55 144 1106 17 55 144 2106
Connectors with flange with coding 2	72	3.35	17 52 072 1107 17 52 072 2107
	144	3.35	17 55 144 1107 17 55 144 2107
Connectors with flange with coding 3 (= coding 1 + 2)	72	3.35	17 52 072 1108 17 52 072 2108
	144	3.35	17 55 144 1108 17 55 144 2108