

General information

Type	B, Q	C, R	D
Wiring side (Rear side)	Input access from the front side via a female connector	Input access via a female connector	Input access from the front side via a female connector Piggyback connector
Soldering technique for a flexible wiring			
Soldering technique for pcb Press-in technique for pcb			
Crimp connections			
Wrapped connections posts 0.6 x 0.6 mm 1 x 1 mm			
Middle section 			
Front side 			

1) Screw fixing (cheesehead screw M 2.5 x 16 + nut) 09 02 000 9909

2) 2 x screw fixing (cylindric screw M 2.5 x 25 DIN EN ISO 1207 + nut M 2.5 DIN EN ISO 4032)

3) Fixing brackets for latching and screw fixing

4) Screw length depends on the pcb thickness

f = female connector
m = male connector
R = right hand
L = left hand