

<i>harbus</i> 64	E		H	
<p>Input access from the front side via a female connector</p>	<p>Input access via a female connector</p> <p>Piggyback connector</p>		<p>Input access from the front side via a female connector</p>	
			<p>I element</p>	
	<p>1 x 1 mm</p>			
<p>Y =</p>	<p>Combinations</p>	<p>Fixing bracket c for male connectors</p> <p>Multiple fixing</p> <p>Single fixing</p>	<p>I element</p>	<p>U element</p>
<p>Housing C</p>	<p>latchable</p>	<p>latch and screw fixing (M 2.5 x 16)</p>	<p>latch and screw fixing</p>	<p>latch and screw fixing</p>
<p>Housing G</p>		<p>screw fixing</p>	<p>screw fixing</p>	<p>screw fixing</p>