

Number of contacts

64



Female connectors

DIN Signal up to 2 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for insulation displacement	64	Performance level 2 ¹⁾ 09 02 264 6828		
		Performance level 3 ¹⁾ 09 02 264 7828		
Strain relief (metal)		09 03 000 9940		
Panel cut out				
Flat cable AWG 28/7				²⁾ Termination area spacing = 508 mm Important: always store reels vertically
grey 30.48 m	64	09 18 064 7001	Wire (tinned) Gauge AWG 28/7 Insulation material as per UL style PVC	Cu AWG 28/7 0.089 mm ²
grey 100.00 m	64	09 18 064 7004		
colour coded 30.48 m	64	09 18 064 7005		
twisted pair ²⁾ 30.48 m	64	09 18 064 7006		
Round flat cable ³⁾				³⁾ Termination area spacing = 100 mm
with screening 30.48 m	64	09 18 064 7007		
screening 100.00 m	64	09 18 064 7010		
without screening 30.48 m	64	09 18 064 7008		
screening 100.00 m	64	09 18 064 7011		
Bench press		09 99 000 0114		
Base plate		09 99 000 0150		
Cable cutter		09 99 000 0116		
Spare parts				
Blade		09 99 000 0179		
Cutting plate		09 99 000 0180		