

Number of contacts

max. 48

Ⓛ



Ⓜ



Accessories

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm																
Female FC crimp contacts individual contacts ¹⁾ FC1 FC2 FC3 Bandoliered contacts (approx. 2,500 pcs.) FC1 FC2 FC3		09 06 000 6464 09 06 000 6461 09 06 000 6462 09 06 000 6454 09 06 000 6451 09 06 000 6452	<table border="1"> <thead> <tr> <th>Identification</th> <th>Wire gauge mm²</th> <th>AWG</th> <th>Insulations ø mm</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>0.09-0.25</td> <td>28-24</td> <td>0.7-1.5</td> </tr> <tr> <td>2</td> <td>0.14-0.56</td> <td>26-20</td> <td>0.8-2.0</td> </tr> <tr> <td>3</td> <td>0.50-1.50</td> <td>20-16</td> <td>1.6-2.8</td> </tr> </tbody> </table> <p>3.5 + 0.5 mm of insulation is stripped from the wires to be crimped. For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2) Crimping tools see chapter 30</p>	Identification	Wire gauge mm ²	AWG	Insulations ø mm	1	0.09-0.25	28-24	0.7-1.5	2	0.14-0.56	26-20	0.8-2.0	3	0.50-1.50	20-16	1.6-2.8	
Identification	Wire gauge mm ²	AWG	Insulations ø mm																	
1	0.09-0.25	28-24	0.7-1.5																	
2	0.14-0.56	26-20	0.8-2.0																	
3	0.50-1.50	20-16	1.6-2.8																	
Mateable with 1 x 1 mm wrap posts																				
Distance fixing brackets for female connectors Type D Type E		top (pos. 2) 09 04 000 9907 ¹⁾ bottom (pos. 32) 09 04 000 9906 ¹⁾																		
Type F Ⓛ Ⓜ		top (pos. 2) 09 06 000 9936 ¹⁾ bottom (pos. 32) 09 06 000 9937 ¹⁾																		

DIN Power up to 6 A

¹⁾ Packaging unit 1,000 pieces
²⁾ Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2