

Number of contacts

15



Female connectors

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm						
Female connector "low profile" with solder pins ³⁾		Performance level 1 acc. to IEC 60 603-2								
2.7 mm	15	09 06 215 2812 ¹⁾		<table border="1"> <tr><td>a</td></tr> <tr><td>2.7</td></tr> <tr><td>4</td></tr> <tr><td>5.5</td></tr> <tr><td>7</td></tr> <tr><td>10</td></tr> </table>	a	2.7	4	5.5	7	10
a										
2.7										
4										
5.5										
7										
10										
4 mm	15	09 06 215 2821 ¹⁾ 09 06 215 2821 222 ¹⁾¹⁾ 09 06 215 2892 ²⁾ 09 06 215 2892 222 ²⁾¹⁾								
5.5 mm	15	09 06 215 2890 ²⁾								
7 mm	15	09 06 215 2831 ¹⁾ 09 06 215 2891 ²⁾								
10 mm	15	09 06 215 2841 ¹⁾								
Board drillings Mounting side										
			<p>Contact arrangement View from termination side</p>							

DIN Power up to 15 A

¹⁾ Variant with silver plated contacts
²⁾ Variant with gold plated contacts
³⁾ With shroud coding, see chapter 00

¹⁾ Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2