





Identification	Part No.	Drawing	Dimensions in mm
<p>HARTING crimping tool for bandoliered contacts (500 pieces) BC / har-bus® 64</p> <p>for bandoliered contacts (250 pieces)</p> <p>FC 1</p> <p>FC 2</p> <p>FC 3</p> <p>BC / har-bus® 64 solid wire</p>	<p>09 99 000 0248</p> <p>09 99 000 0247</p> <p>09 99 000 0119</p> <p>09 99 000 0120</p> <p>09 99 000 0627</p>	<p>Wire gauge 0.09 - 0.5 mm²</p> <p>Wire gauge 0.09 - 0.25 mm²</p> <p>0.14 - 0.56 mm²</p> <p>0.50 - 1.50 mm²</p> <p>0.13 mm² (solid wire)</p>	
<p>HARTING semi-automatic crimping device</p> <p>Main drive, foot-operated 115/230 V – 50 Hz</p> <p>Real holder for 2,500 contacts FC 1, FC 2 or FC 3 and for 5,000 contacts BC / har-bus® 64</p>	<p>09 99 000 0246</p> <p>09 99 000 0158</p>	<p>Locator not necessary</p>	
<p>Crimping head for bandoliered contacts BC / har-bus® 64</p> <p>FC 1</p> <p>FC 2</p> <p>FC 3</p> <p>BC/har-bus® 64 solid wire</p>	<p>09 99 000 0252</p> <p>09 99 000 0249</p> <p>09 99 000 0250</p> <p>09 99 000 0251</p> <p>09 99 000 0628</p>	<p>Wire gauge 0.09 - 0.5 mm²</p> <p>0.09 - 0.25 mm²</p> <p>0.14 - 0.56 mm²</p> <p>0.5 - 1.5 mm²</p> <p>0.13 mm² (solid wire)</p>	
<p>Insertion tool</p> <p>for contacts BC / har-bus® 64</p> <p>for contacts FC 1, FC 2 and FC 3</p>	<p>09 99 000 0100</p> <p>09 99 000 0088</p>		
<p>Removal tool</p> <p>for contacts BC / har-bus® 64</p> <p>for contacts FC 1, FC 2 and FC 3</p>	<p>09 99 000 0101</p> <p>09 99 000 0087</p>		