

Identification	for use with	Part No.	Drawing	Dimensions in mm															
Removal tool for moulding	<b>Male connectors</b> Type Q, 2Q, 3Q R, 2R, 3R	09 99 000 0198		12															
Removal tool for single male contacts		09 99 000 0239																	
Insertion tool for single male press-in contacts		09 99 000 0200		50 40 11															
Press-out tool	<b>Termination length</b>																		
	17 mm	09 99 000 0197																	
	13 - 13.2 mm	09 99 000 0219																	
	11.5 mm	09 99 000 0221																	
	4.5 - 5.3 mm	09 99 000 0220																	
			<table border="1"> <thead> <tr> <th>Termination length [mm]</th> <th>x [mm]</th> <th>y [mm]</th> </tr> </thead> <tbody> <tr> <td>17</td> <td>12</td> <td>18.7</td> </tr> <tr> <td>13 - 13.2</td> <td>12</td> <td>22.7</td> </tr> <tr> <td>11.5</td> <td>14</td> <td>20.1</td> </tr> <tr> <td>4.5 - 5.3</td> <td>12</td> <td>30.2</td> </tr> </tbody> </table>	Termination length [mm]	x [mm]	y [mm]	17	12	18.7	13 - 13.2	12	22.7	11.5	14	20.1	4.5 - 5.3	12	30.2	
Termination length [mm]	x [mm]	y [mm]																	
17	12	18.7																	
13 - 13.2	12	22.7																	
11.5	14	20.1																	
4.5 - 5.3	12	30.2																	
			With the different dimension y no adjustment of hand bench press necessary.																
Termination support for protection against bending of 13 mm - 17 mm terminations	<b>Male connectors</b> Type Q, 2Q, 3Q R, 2R, 3R	09 99 000 0240		11 95 5,4															
	<b>Female connectors</b> Type B, 2B, 3B C, 2C, 3C																		
	<b>Female connectors</b> Type F	09 99 000 0241		14,8 87,5 4,8															
Support block for repair and removal	<b>Male connectors</b> Type Q, 2Q, 3Q R, 2R, 3R SEK 18*	09 99 000 0218		40 100 26 40,7															
	<b>Female connectors</b> Type B, 2B, 3B C, 2C, 3C F																		

\* Connectors see separate catalogue