




Number of contacts

Mounting height

Low-Profile Versions

9-37  
50



Turned solder pins, angled with snap-in-clips and grounding board locks


Identification

Drawing


Dimensions in mm

Male connector



9-37 50  
Mating face acc. to: DIN 41 652 · CECC 75 301-802 · IEC 60 807  
No. 1 contact




Grounding board lock 0.2 x 0.6




Dimples





fitted screw locks  
4 - 40 UNC



M3 or  
4 - 40 UNC



Board drillings



	a	b±0.1	c	f
9	30.90	25.00	12.50	2.74
15	39.20	33.30	12.50	2.74
25	53.10	47.00	12.50	2.76
37	69.40	63.50	12.50	2.76
50	67.00	61.10	15.70	2.76