



Straight power contacts for cable applications

Identification	Rating (A)	Part No.	
<b>Performance levels</b> ▶		<b>Performance level 3</b>	<b>S4<sup>1)</sup></b>
<b>Solder version</b>			
<b>Male contacts</b>	10 20 30 40	09 69 281 7420 09 69 281 7421 09 69 281 7422 09 69 281 7423	09 69 281 5420 09 69 281 5421 09 69 281 5422 09 69 281 5423
<b>Short male contacts</b>	20 40	09 69 281 7821 09 69 281 7823	09 69 281 5821 09 69 281 5823
<b>Female contacts</b>	10 20 30 40	09 69 181 7420 09 69 181 7421 09 69 181 7422 09 69 181 7423	09 69 181 5420 09 69 181 5421 09 69 181 5422 09 69 181 5423
<b>Short female contacts</b>	20 40	09 69 181 7821 09 69 181 7823	09 69 181 5821 09 69 181 5823
<b>Crimp version<sup>2)</sup></b>			
<b>Male contacts</b>	10 20 30 40	09 69 282 7420 09 69 282 7421 09 69 282 7422 09 69 282 7423	09 69 282 5420 09 69 282 5421 09 69 282 5422 09 69 282 5423
<b>Short male contacts</b>	20 40	09 69 282 7821 09 69 282 7823	09 69 282 5821 09 69 282 5823
<b>Female contacts</b>	10 20 30 40	09 69 182 7420 09 69 182 7421 09 69 182 7422 09 69 182 7423	09 69 182 5420 09 69 182 5421 09 69 182 5422 09 69 182 5423
<b>Short female contacts</b>	20 40	09 69 182 7821 09 69 182 7823	09 69 182 5821 09 69 182 5823

D-Sub - M

<sup>1)</sup> S4 = 0.76 µm Au or PdNi equivalent  
<sup>2)</sup> Tooling see chapter 31