

Number of contacts 2, 3, 5, 7, 8, 9, 11, 13, 17, 21, 24, 25, 27, 36, 43

Approvals DIN 41 652, part 1

Working current 5 A for signal contacts

Temperature range -55 °C ... + 125 °C  
The higher temperature limit includes the ambient and heating effect of the contacts under load

Materials  
Mouldings Thermoplastic resin, glass-fibre filled (Polyester)  
UL 94-V0  
color: green for standard  
black for crimp

Metal shell Plated steel

