

Number of contacts

9-50



IP 67, straight turned solder pins,
with rear metal mounting plate, spacer and board lock

Identification	No. of contacts	Part No.	
		S4 ¹⁾	
Male connector metal shell with dimples			
	9	09 67 609	. 675
	15	09 67 615	. 675
	25	09 67 625	. 675
	37	09 67 637	. 675
	50	09 67 650	. 675
Please insert digit for flange thread			
4-40 UNC ▶	7		
M3 ▶	9		
Female connector metal shell			
	9	09 67 609	. 775
	15	09 67 615	. 775
	25	09 67 625	. 775
	37	09 67 637	. 775
	50	09 67 650	. 775
Please insert digit for flange thread			
4-40 UNC ▶	6		
M3 ▶	8		

D-Sub - W

¹⁾ S4 = 0.76 µm (30 µinch) Au or PdNi equivalent