



Top and side entry hoods with knurled screws

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																																																
<b>Top entry hood</b> Black thermoplastic	9	09 67 009 042		<table border="1"> <thead> <tr> <th></th> <th>A1</th> <th>A2</th> <th>B</th> <th>C1</th> <th>C2</th> <th>max. Ø 1</th> <th>max. Ø 2</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>31.5</td> <td>32.5</td> <td>15</td> <td>34</td> <td>38</td> <td>8.0</td> <td>11.5</td> </tr> <tr> <td>15</td> <td>40.0</td> <td>41.0</td> <td>15</td> <td>34</td> <td>38</td> <td>11.5</td> <td>11.5</td> </tr> <tr> <td>25</td> <td>53.5</td> <td>54.5</td> <td>15</td> <td>40</td> <td>40</td> <td>11.5</td> <td>11.5</td> </tr> <tr> <td>37</td> <td>71.0</td> <td>71.0</td> <td>15</td> <td>40</td> <td>40</td> <td>11.5</td> <td>11.5</td> </tr> <tr> <td>50</td> <td>67.5</td> <td></td> <td>19</td> <td>40</td> <td></td> <td>14.0</td> <td></td> </tr> </tbody> </table>		A1	A2	B	C1	C2	max. Ø 1	max. Ø 2	9	31.5	32.5	15	34	38	8.0	11.5	15	40.0	41.0	15	34	38	11.5	11.5	25	53.5	54.5	15	40	40	11.5	11.5	37	71.0	71.0	15	40	40	11.5	11.5	50	67.5		19	40		14.0	
	A1	A2			B	C1	C2	max. Ø 1	max. Ø 2																																											
9	31.5	32.5			15	34	38	8.0	11.5																																											
15	40.0	41.0			15	34	38	11.5	11.5																																											
25	53.5	54.5			15	40	40	11.5	11.5																																											
37	71.0	71.0	15	40	40	11.5	11.5																																													
50	67.5		19	40		14.0																																														
Please insert digit for screw option	15	09 67 015 042																																																		
	25	09 67 025 042																																																		
	37	09 67 037 042																																																		
Knurled screw, thread 4-40 UNC ▶ 4 Knurled screw, thread M3 ▶ 6	50	09 67 050 042																																																		
<b>Top entry hood</b> Metallized thermoplastic	9	09 67 009 042																																																		
Please insert digit for screw option	15	09 67 015 042																																																		
	25	09 67 025 042																																																		
	37	09 67 037 042																																																		
Knurled screw, thread 4-40 UNC ▶ 5 Knurled screw, thread M3 ▶ 7																																																				
<b>Top and side entry hood</b> Black thermoplastic	9 <sup>3)</sup>	09 67 009 043																																																		
	15	09 67 015 043																																																		
	25	09 67 025 043																																																		
	37 <sup>1)</sup>	09 67 037 043																																																		
Please insert digit for screw option Knurled screw, thread 4-40 UNC ▶ 4 Knurled screw, thread M3 ▶ 0																																																				
<b>Top and side entry hood</b> Metallized thermoplastic	9 <sup>3)</sup>	09 67 009 043		<table border="1"> <thead> <tr> <th></th> <th>A</th> <th>B</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>31.5</td> <td>40</td> </tr> <tr> <td>15</td> <td>40.0</td> <td>40</td> </tr> <tr> <td>25</td> <td>53.5</td> <td>43</td> </tr> <tr> <td>37</td> <td>71.3</td> <td>40</td> </tr> </tbody> </table>		A	B	9	31.5	40	15	40.0	40	25	53.5	43	37	71.3	40																																	
	A	B																																																		
9	31.5	40																																																		
15	40.0	40																																																		
25	53.5	43																																																		
37	71.3	40																																																		
	15	09 67 015 043																																																		
	25 <sup>2)</sup>	09 67 025 043																																																		
	37 <sup>1)</sup>	09 67 037 043																																																		
Please insert digit for screw option Knurled screw, thread 4-40 UNC ▶ 5 Knurled screw, thread M3 ▶ 1																																																				

1) 37 pole is only available with side entry and with knurled screw, thread 4-40 UNC  
 2) Cable clamp kit for two outputs is available as accessories (it includes: screw, metal clamp, plastic insert and grommet). With Part No. 09 67 001 9988 ten of these kits are delivered.  
 3) 9 pole hood provided with only one screw on the opposite side of the cable entry.