



Top and side entry hoods with short screws

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																								
Top and side entry hood Black thermoplastic Please insert digit for screw option Short screw, thread 4-40 UNC ▶ 3 Short screw, thread M3 ▶ 2	9 ¹⁾ 15 25 37	09 67 009 046 . 09 67 015 046 . 09 67 025 046 . 09 67 037 046 .		<table border="1"> <thead> <tr> <th></th> <th>A</th> <th>B</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>31.5</td> <td>40</td> </tr> <tr> <td>15</td> <td>40.0</td> <td>40</td> </tr> <tr> <td>25</td> <td>53.5</td> <td>43</td> </tr> <tr> <td>37</td> <td>71.3</td> <td>40</td> </tr> </tbody> </table>		A	B	9	31.5	40	15	40.0	40	25	53.5	43	37	71.3	40									
	A	B																										
9	31.5	40																										
15	40.0	40																										
25	53.5	43																										
37	71.3	40																										
Top and side entry hood Metallized thermoplastic Please insert digit for screw option Short screw, thread 4-40 UNC ▶ 5 Short screw, thread M3 ▶ 4	9 ¹⁾ 15 25 37	09 67 009 046 . 09 67 015 046 . 09 67 025 046 . 09 67 037 046 .																										
Spares Knurled screw, thread 4-40 UNC Insert for metallized hoods Cable clamp Cable clamp screw	9-25 9-15 25-37 9-15 25-37 9-37	09 67 002 9081 09 67 002 9103 09 67 002 9105 09 67 002 9104 09 67 002 9106 09 67 002 9102																										
Grommet for black thermoplastic hood for metallized hood		09 67 001 9968 09 67 002 9075		<table border="1"> <thead> <tr> <th colspan="2">max. Ø</th> </tr> <tr> <th>... 9968</th> <th>... 9075</th> </tr> </thead> <tbody> <tr> <td>3.3</td> <td>3.5</td> </tr> <tr> <td>4.3</td> <td>4.5</td> </tr> <tr> <td>5.3</td> <td>5.5</td> </tr> <tr> <td>6.3</td> <td>6.5</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th colspan="2">max. Ø</th> </tr> <tr> <th>... 9968</th> <th>... 9075</th> </tr> </thead> <tbody> <tr> <td>7.3</td> <td>7.5</td> </tr> <tr> <td>8.3</td> <td>8.5</td> </tr> <tr> <td>9.3</td> <td>9.5</td> </tr> <tr> <td>10.3</td> <td>10.5</td> </tr> </tbody> </table>	max. Ø		... 9968	... 9075	3.3	3.5	4.3	4.5	5.3	5.5	6.3	6.5	max. Ø		... 9968	... 9075	7.3	7.5	8.3	8.5	9.3	9.5	10.3	10.5
max. Ø																												
... 9968	... 9075																											
3.3	3.5																											
4.3	4.5																											
5.3	5.5																											
6.3	6.5																											
max. Ø																												
... 9968	... 9075																											
7.3	7.5																											
8.3	8.5																											
9.3	9.5																											
10.3	10.5																											

¹⁾ 9 pole hood provided with only one screw on the opposite side of the cable entry.
 Operating temperature for all hoods on this page: -55 °C ... +110 °C