

Number of contacts

9–37



SMT stamped solder pins, straight with grounding pins

Identification	No. of contacts	Part No.	
Performance levels Explanations see page 21.02 Other performance levels on request		Performance level 3	
		Performance level 2	
Male connector metal shell with dimples			
	9	09 55 169 78 .. 741	09 55 169 68 .. 741
	15	09 55 269 78 .. 741	09 55 269 68 .. 741
	25	09 55 369 78 .. 741	09 55 369 68 .. 741
	37	09 55 469 78 .. 741	09 55 469 68 .. 741
Female connector metal shell			
	9	09 55 155 76 .. 741	09 55 155 66 .. 741
	15	09 55 255 76 .. 741	09 55 255 66 .. 741
	25	09 55 355 76 .. 741	09 55 355 66 .. 741
	37	09 55 455 76 .. 741	09 55 455 66 .. 741
Please insert digit for flange thread or fitted female screw locks			
	M3 ▶ 11		
	4-40 UNC ▶ 12		
	fixed screw locks M3 ▶ 21		
	fixed screw locks 4-40 UNC ▶ 22		

SMT technology