

Number of contacts

9–37



SMT stamped solder pins, angled with grounding board locks

Identification	No. of contacts	Part No.	
Performance levels Explanations see page 21.02 Other performance levels on request		Performance level 3	
		Performance level 2	
Male connector metal shell with dimples			
	9	09 55 166 78 .. 741	09 55 166 68 .. 741
	15	09 55 266 78 .. 741	09 55 266 68 .. 741
	25	09 55 366 78 .. 741	09 55 366 68 .. 741
	37	09 55 466 78 .. 741	09 55 466 68 .. 741
Female connector metal shell			
	9	09 55 156 76 .. 741	09 55 156 66 .. 741
	15	09 55 256 76 .. 741	09 55 256 66 .. 741
	25	09 55 356 76 .. 741	09 55 356 66 .. 741
	37	09 55 456 76 .. 741	09 55 456 66 .. 741
Please insert digit for flange thread or fitted female screw locks			
M3 ▶ 15			
4-40 UNC ▶ 16			
non-removable fitted screw locks M3 ▶ 19			
non-removable fitted screw locks 4-40 UNC ▶ 20			

SMT
technology