

Number of contacts

6-64



SMC male header with angled solder pins

Identification	No. of contacts	Part No.					
		Without levers		With short levers		With long levers	
SMC male header with angled solder pins Length: 2.9 mm	6	09 19 506	└ 923	09 19 506	└ 913	09 19 506	└ 903
	10	09 19 510	└ 923	09 19 510	└ 913	09 19 510	└ 903
	14	09 19 514	└ 923	09 19 514	└ 913	09 19 514	└ 903
	16	09 19 516	└ 923	09 19 516	└ 913	09 19 516	└ 903
	20	09 19 520	└ 923	09 19 520	└ 913	09 19 520	└ 903
	24	09 19 524	└ 923	09 19 524	└ 913	09 19 524	└ 903
	26	09 19 526	└ 923	09 19 526	└ 913	09 19 526	└ 903
	30	09 19 530	└ 923	09 19 530	└ 913	09 19 530	└ 903
	34	09 19 534	└ 923	09 19 534	└ 913	09 19 534	└ 903
	40	09 19 540	└ 923	09 19 540	└ 913	09 19 540	└ 903
	50	09 19 550	└ 923	09 19 550	└ 913	09 19 550	└ 903
	60	09 19 560	└ 923	09 19 560	└ 913	09 19 560	└ 903
	64	09 19 564	└ 923	09 19 564	└ 913	09 19 564	└ 903

SMC technology

22
22

Kinked version on request

* Not normally kept in stock
For accessories see page 22.30
For dimensions see page 22.21

For performance level 3 please specify digit 7*
For performance level 2 please specify digit 6*
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

