


Number of contacts

6-64



SMC male header with straight solder pins, kinked

Identification	No. of contacts	Part No.					
		Without levers		With short levers		With long levers	
SMC male header with straight solder pins, kinked Length: 2.9 mm	6	09 19 506	└ 024	09 19 506	└ 014	09 19 506	└ 004
	10	09 19 510	└ 024	09 19 510	└ 014	09 19 510	└ 004
	14	09 19 514	└ 024	09 19 514	└ 014	09 19 514	└ 004
	16	09 19 516	└ 024	09 19 516	└ 014	09 19 516	└ 004
	20	09 19 520	└ 024	09 19 520	└ 014	09 19 520	└ 004
	24	09 19 524	└ 024	09 19 524	└ 014	09 19 524	└ 004
	26	09 19 526	└ 024	09 19 526	└ 014	09 19 526	└ 004
	30	09 19 530	└ 024	09 19 530	└ 014	09 19 530	└ 004
	34	09 19 534	└ 024	09 19 534	└ 014	09 19 534	└ 004
	40	09 19 540	└ 024	09 19 540	└ 014	09 19 540	└ 004
	50	09 19 550	└ 024	09 19 550	└ 014	09 19 550	└ 004
	60	09 19 560	└ 024	09 19 560	└ 014	09 19 560	└ 004
	64	09 19 564	└ 024	09 19 564	└ 014	09 19 564	└ 004

SMC technology

* Not normally kept in stock
For accessories see page 22.30
For dimensions see page 22.25

For performance level 3 please specify digit 7
For performance level 2 please specify digit 6
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

