

Specific tooling for SEK male low-profile

Identification	Part No.	Drawing	Dimensions in mm
Bottom tool narrow for SEK	09 99 000 0256		
Top tool for SEK male low-profile connectors	6 way 09 99 000 0 06 10 way 09 99 000 0 10 14 way 09 99 000 0 14 16 way 09 99 000 0 16 20 way 09 99 000 0 20 26 way 09 99 000 0 26 34 way 09 99 000 0 34 40 way 09 99 000 0 40 50 way 09 99 000 0 50 60 way 09 99 000 0 60 64 way 09 99 000 0 64	Top tool including insert <p>X Length depends on number of contacts</p>	
Top tool including insert ➤ 4 Modular insert ➤ 5		Modular insert 	
Press-out tool for complete SEK male connectors with 5.5 mm terminations	09 99 000 0220		
Support block	09 99 000 0218		