



Identification	for use with	Part No.	Wire gauge [mm ²]	AWG	Insulation [Ø mm]
Crimping tool					
for DIN 41 612 connectors ¹⁾	contacts BC	09 98 000 3004	0.09 - 0.56	28 - 20	0.7 - 1.6
	contacts FC 1	09 98 000 3005	0.09 - 0.25	28 - 24	0.7 - 1.6
	FC 2	09 98 000 3006	0.14 - 0.56	26 - 20	0.8 - 2.3
	FC 3	09 98 000 3007	0.50 - 1.50	20 - 16	1.6 - 2.8
	for D-Sub connectors ²⁾	standard contacts	09 98 000 3008 09 98 000 3009	0.09 - 0.25 0.25 - 0.56	28 - 24 24 - 20
	high density contacts	09 98 000 3012		26 - 24	0.8 - 1.4

¹⁾ 3.5 + 0.5 mm of insulation is stripped from the wire to be crimped
²⁾ 2.5 + 0.5 mm of insulation is stripped from the wire to be crimped