



Cable assemblies


Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

Cable assembly D-Sub HD 78 pole

Hood: shielded plastic hood with side entry, screw 4-40 UNC
 Cable: 39 twisted pairs, AWG 26, double shielded, PVC
 Wiring: 1:1

Length: L = 0.5 m
 L = 1.0 m
 L = 2.0 m
 L = 5.0 m
 L = 10.0 m
 L = 20.0 m

33 56 212 0050 028
 33 56 213 1000 002
 33 56 213 2000 016
 33 56 212 0500 029
 33 56 212 1000 030
 33 56 212 2000 031




Cable assembly D-Sub HD 44 pole

Hood: shielded plastic hood with side entry, screw 4-40 UNC
 Cable: 22 twisted pairs, AWG 26, double shielded, PVC
 Wiring: 1:1

Length: L = 0.5 m
 L = 1.0 m
 L = 1.5 m
 L = 2.0 m
 L = 5.0 m
 L = 10.0 m

33 56 213 0500 023
 33 56 213 1000 024
 33 56 213 1500 022
 33 56 213 2000 025
 33 56 213 5000 026
 33 56 212 1000 027



Cable assembly D-Sub HD 44 pole

Hood: metal hood with top entry, screw 4-40 UNC
 Cable: 24 twisted pairs, AWG 26, double shielded, PVC
 Wiring: 1:1

Length: L = 0.5 m
 L = 1.0 m
 L = 5.0 m
 L = 10.0 m
 L = 20.0 m

33 56 212 0050 032
 33 56 212 0100 033
 33 56 212 0500 034
 33 56 212 1000 035
 33 56 212 2000 036

