



Cable assemblies


Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

**Cable assembly D-Sub HD
44 pole**

Hood: overmoulded
with side entry
Cable: 24 twisted pairs, solid
wires, AWG 26, shielded,
halogen free
Wiring: 1:1

Length: L = 0.5 m
L = 1.0 m
L = 2.0 m
L = 5.0 m

33 56 224 5000 001
33 56 221 0010 001
33 56 221 0020 001
33 56 221 0050 001



**Cable assembly D-Sub
9 pole**

Hood: shielded plastic hood
with side entry,
screw 4-40 UNC
Cable: 5 twisted pairs,
stranded, AWG 24, shielded,
PVC
Wiring: 1:1

Length: L = 0.5 m
L = 1.0 m
L = 1.5 m
L = 2.0 m
L = 5.0 m

33 66 214 5000 058
33 66 213 1000 059
33 66 213 1500 060
33 66 213 2000 061
33 66 213 5000 062

