

DIN 41612 Signal crimp contact type			BC crimp contacts 09 02 000						har-bus® 64 crimp contacts 02 05 000					
Part number	Female contacts	PL 1	6474	8444	8474	6474	8444	8474	1511	1512	1513	1511	1512	1513
		PL 2	6484	8434	8484	6484	8434	8484	2511	2512	2513	2511	2512	2513
Bandoliered contacts: 5,000 pieces/reel			X			X			X			X		
Bandoliered contacts: 500 pieces/reel				X			X			X			X	
Individual contacts					X			X			X			X
Cable diameter		mm ²	0.09-0.5			0.13 mm ² solid wire			0.09-0.5			0.13 mm ² solid wire		
		AWG	28-20						28-20					
Hand crimp tool		09 99 000 0075			X						X			
		09 99 000 0248		X						X				
		09 99 000 0627					X						X	
Hand crimp tool 09 99 000 0620 with insert		09 99 000 0621			X						X			
		09 99 000 0629						X						X
Semi automatic crimp tool 09 99 000 0246 with head		09 99 000 0252	X	X					X	X				
		09 99 000 0628				X	X					X	X	
and reel holder		09 99 000 0158	X			X			X			X		
Automatic crimp machine type BK 09 98 000 5000 with tools		09 98 000 3004	X			X			X			X		
Insertion tool		09 99 000 0100				X						X		
Removal tool		09 99 000 0101				X						X		

DIN 41612 Power crimp contacts			FC crimp contacts 09 06 000									
Part number	Female contacts	PL 1	6474	7474	8474	6471	7471	8471	6472	7472	8472	
		PL 2	6484	7484	8484	6481	7481	8481	6482	7482	8482	
	Male contacts	PL 1	9544	–	9554	9541	5541	9551	9542	5542	9552	
		PL 2	9564	–	9574	9561	–	9571	9562	–	9572	
Female contacts for 1 x 1 wire wrap posts		–	6454	–	6464	6451	–	6461	6452	–	6462	
Bandoliered contacts: 2,500 pieces/reel			X			X			X			
Bandoliered contacts: 250 pieces/reel				X			X			X		
Individual contacts					X			X			X	
Cable diameter		mm ²	0.09-0.25			0.14-0.56			0.5-1.5			
		AWG	28-24			26-20			20-16			
Hand crimp tool		09 99 000 0075			X							
		09 99 000 0076						X				
		09 99 000 0077									X	
		09 99 000 0191			X				X			X
		09 99 000 0247		X								
		09 99 000 0119						X				
		09 99 000 0120									X	
Hand crimp tool 09 99 000 0620 with insert		09 99 000 0621			X							
		09 99 000 0622						X				
		09 99 000 0623									X	
Semi automatic crimp tool 09 99 000 0246 with head		09 99 000 0249	X	X								
		09 99 000 0250				X	X					
		09 99 000 0251							X	X		
and reel holder		09 99 000 0158	X			X			X			
Automatic crimp machine type BK 09 98 000 5000 with tools		09 98 000 3005	X									
		09 98 000 3006				X						
		09 98 000 3007							X			
Insertion tool		09 99 000 0088		X			X			X		
Removal tool		09 99 000 0087		X			X			X		