



## Accessories

### Ha-VIS SFP modules 1000 Mbit/s

#### SFP:

Type	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s MM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM
Wave length	850 nm	1310 nm	1310 nm	1310 nm
Mode	Multimode	Singlemode	Singlemode	Singlemode
Fiber	50 / 125 µm or 62.5 / 125 µm	9 / 125 µm	9 / 125 µm	9 / 125 µm
Max. cable length*	550 m (50 / 125) 275 m (62.5 / 125)	10 km	40 km	80 km
Connector	LC connector duplex	LC connector duplex	LC connector duplex	LC connector duplex
Optical budget	min. 9 dB	min. 9 dB	min. 9 dB	min. 9 dB
Data rate	1250 Mbit/s	1250 Mbit/s	1250 Mbit/s	1250 Mbit/s

\* Typical cable length depending on attenuation of each specific application.

Identification	Part number	Drawing	Dimensions in mm
<b>SFP modules</b>			
SFP Gigabit Ethernet Transceiver 1,25 Gbit/s MM	20 76 010 0300		
SFP Gigabit Ethernet Transceiver 1,25 Gbit/s SM	20 76 030 0300		
SFP Gigabit Ethernet Transceiver L40 1,25 Gbit/s SM	20 76 034 0300		
SFP Gigabit Ethernet Transceiver L80 1,25 Gbit/s SM	20 76 038 0300		
other types on request			