

Identification	Part No.	Drawing	Dimensions in mm
<p>Mounting possibilities for code comb at the male connector with fixing brackets</p>			
<p>Fixing brackets B for male connectors* for 19" racks according to DIN EN 60297, part 3-101</p> <p>Single fixing* without nut</p> <p>with nut M 2.5 DIN 562</p>	<p>left 09 06 000 9909</p> <p>right 09 06 000 9910</p> <p>left 09 06 001 9934</p> <p>right 09 06 001 9935</p>		
<p>Multiple fixing* without coding at the fixing bracket without nut</p> <p>without coding at the fixing bracket with nut M 2.5 DIN 562</p> <p>with coding at fixing bracket<sup>1)</sup> with nut M 2.5 DIN 562</p> <p>15 mm 20 mm</p> <p>15 mm 20 mm</p>	<p>left 09 06 000 9907</p> <p>right 09 06 000 9908</p> <p>left 09 06 000 9966</p> <p>right 09 06 000 9967</p> <p>left 09 06 000 9995 09 06 000 9997</p> <p>right 09 06 000 9996 09 06 000 9998</p>		<p>mounting examples</p> <p>09 06 000 9995    09 06 000 9997</p> <p>2) supplied with fixing</p>
<p>Protection and fixing strip* for 20 mm shell housing Single fixing fits female connectors and I element crimp</p>	<p>09 06 001 9909</p>		

\* Fits D 20/2 and D 20/4  
<sup>1)</sup> Specific coding between the fixing bracket and the pcb guiding rail.  
 The guiding rail and corresponding coding pins are not scope of delivery