


Number of contacts

max. 24



Interface connector I

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
<p>Interface connector I for male crimp contacts</p> <p>Order contacts separately</p>	24	09 26 024 3411		

DIN Power up to 6 A

Identification	Identification Wire gauge	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00
			2 1
<p>Male crimp FC contacts</p> <p>Bandoliered contacts (approx. 2,500 pieces)</p> <p>Bandoliered contacts (approx. 250 pieces)</p> <p>Individual contacts¹⁾</p>	<p>1</p> <p>2</p> <p>3</p> <p>2</p> <p>3</p> <p>1</p> <p>2</p> <p>3</p>	<p>09 06 000 9564</p> <p>09 06 000 9561</p> <p>09 06 000 9562</p> <p>09 06 000 5541</p> <p>09 06 000 5542</p> <p>09 06 000 9574</p> <p>09 06 000 9571</p> <p>09 06 000 9572</p>	<p>09 06 000 9544</p> <p>09 06 000 9541</p> <p>09 06 000 9542</p> <p>09 06 000 5541</p> <p>09 06 000 5542</p> <p>09 06 000 9554</p> <p>09 06 000 9551</p> <p>09 06 000 9552</p>

FC	Wire gauge mm ²	AWG	Insulation ø mm	Identification
FC 1	0.09 - 0.25	28 - 24	0.7 - 1.5	<p>Bandoliered contacts</p>
FC 2	0.14 - 0.56	26 - 20	0.8 - 2.0	
FC 3	0.5 - 1.5	20 - 16	1.6 - 2.8	
<p>3.5 + 0.5 mm of insulation is stripped from the wires to be crimped</p> <p>For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2)</p> <p>Insertion, removal and crimping tools see chapter 30</p>				<p>Individual contacts</p>

¹⁾ Packaging unit 1,000 pieces