

## HARTING customer request form

Our innovative technology offers all the possibilities you may need.  
 For customer solutions, please contact your local HARTING representative.  
 Here is a summary of the information we need to develop a customer solution:

### Connector

Standard D-Sub	Gender	<input type="checkbox"/> Male	<input type="checkbox"/> Female			
	No. of contacts	<input type="checkbox"/> 9	<input type="checkbox"/> 15	<input type="checkbox"/> 25	<input type="checkbox"/> 37	<input type="checkbox"/> 50
	Termination	<input type="checkbox"/> Solder bucket	<input type="checkbox"/> Straight pcb	<input type="checkbox"/> R/A Eur, 2.54 mm	<input type="checkbox"/> R/A US, 2.84 mm	

Mixed D-Sub	Gender	<input type="checkbox"/> Male	<input type="checkbox"/> Female		
	Contact arrangement	<input type="checkbox"/> 3W3	<input type="checkbox"/> 3W3C	<input type="checkbox"/> Other _____	
	Power contact rating	<input type="checkbox"/> 10 A	<input type="checkbox"/> 20 A	<input type="checkbox"/> 30 A	<input type="checkbox"/> 40 A
	Termination	<input type="checkbox"/> Solder bucket	<input type="checkbox"/> Straight pcb	<input type="checkbox"/> R/A pcb (please specify the board drillings)	

### Flange thread and board locking options

#### Right angled version

<input type="checkbox"/> Through hole	
<input type="checkbox"/> Clinch nut 4-40 UNC	
<input type="checkbox"/> Clinch nut M3	
<input type="checkbox"/> Bracket	
<input type="checkbox"/> Board lock	
<input type="checkbox"/> Female screw lock 4-40 UNC	
<input type="checkbox"/> Female screw lock M3	

#### Straight version

<input type="checkbox"/> Through hole	
<input type="checkbox"/> Clinch nut 4-40 UNC	
<input type="checkbox"/> Clinch nut M3	
<input type="checkbox"/> Spacer 4-40 UNC	
<input type="checkbox"/> Spacer M3	
<input type="checkbox"/> Female screw lock 4-40 UNC	
<input type="checkbox"/> Spacer 4-40 UNC + board lock	
<input type="checkbox"/> Spacer M3 + board lock	
Spacer + board lock and female screw lock	
<input type="checkbox"/> M3	<input type="checkbox"/> 4-40 UNC