

Accessories – coding system

Identification	Part No.	Panel thickness	Dimensions in mm																																				
Coding¹⁾																																							
Female	09 67 002 9121 xx 1	2.40 - 2.60 mm ³⁾																																					
	09 67 002 9121 xx 2	2.00 - 2.40 mm																																					
	09 67 002 9121 xx 3	1.20 - 2.00 mm																																					
	09 67 002 9121 xx 4	0.80 - 1.20 mm																																					
Male	09 67 002 9122 xx 1	2.40 - 2.60 mm ³⁾																																					
	09 67 002 9122 xx 2	2.00 - 2.40 mm																																					
	09 67 002 9122 xx 3	1.20 - 2.00 mm																																					
	09 67 002 9122 xx 4	0.80 - 1.20 mm																																					
Insert digits for coding configuration, e. g. "C3"		36 coding configurations ²⁾	<table border="1"> <tr> <td>A1</td> <td>B1</td> <td>C1</td> <td>D1</td> <td>E1</td> <td>F1</td> </tr> <tr> <td>A2</td> <td>B2</td> <td>C2</td> <td>D2</td> <td>E2</td> <td>F2</td> </tr> <tr> <td>A3</td> <td>B3</td> <td>C3</td> <td>D3</td> <td>E3</td> <td>F3</td> </tr> <tr> <td>A4</td> <td>B4</td> <td>C4</td> <td>D4</td> <td>E4</td> <td>F4</td> </tr> <tr> <td>A5</td> <td>B5</td> <td>C5</td> <td>D5</td> <td>E5</td> <td>F5</td> </tr> <tr> <td>A6</td> <td>B6</td> <td>C6</td> <td>D6</td> <td>E6</td> <td>F6</td> </tr> </table>	A1	B1	C1	D1	E1	F1	A2	B2	C2	D2	E2	F2	A3	B3	C3	D3	E3	F3	A4	B4	C4	D4	E4	F4	A5	B5	C5	D5	E5	F5	A6	B6	C6	D6	E6	F6
A1	B1	C1	D1	E1	F1																																		
A2	B2	C2	D2	E2	F2																																		
A3	B3	C3	D3	E3	F3																																		
A4	B4	C4	D4	E4	F4																																		
A5	B5	C5	D5	E5	F5																																		
A6	B6	C6	D6	E6	F6																																		
Female screw lock																																							
<table border="1"> <thead> <tr> <th colspan="2">Thread</th> </tr> <tr> <th>inner</th> <th>outer</th> </tr> </thead> <tbody> <tr> <td>4 - 40 UNC</td> <td>4 - 40 UNC</td> </tr> <tr> <td>4 - 40 UNC</td> <td>M3</td> </tr> <tr> <td>M3</td> <td>4 - 40 UNC</td> </tr> <tr> <td>M3</td> <td>M3</td> </tr> </tbody> </table>	Thread		inner	outer	4 - 40 UNC	4 - 40 UNC	4 - 40 UNC	M3	M3	4 - 40 UNC	M3	M3	<table border="1"> <tbody> <tr> <td>09 67 002 9123³⁾</td> <td rowspan="4">2.00 - 2.60 mm</td> </tr> <tr> <td>09 67 002 9124</td> </tr> <tr> <td>09 67 002 9125</td> </tr> <tr> <td>09 67 002 9126</td> </tr> <tr> <td>09 67 002 9129</td> <td rowspan="4">1.20 - 2.00 mm</td> </tr> <tr> <td>09 67 002 9130</td> </tr> <tr> <td>09 67 002 9131</td> </tr> <tr> <td>09 67 002 9132</td> </tr> <tr> <td>09 67 002 9133</td> <td rowspan="4">0.80 - 1.20 mm</td> </tr> <tr> <td>09 67 002 9134</td> </tr> <tr> <td>09 67 002 9135</td> </tr> <tr> <td>09 67 002 9136</td> </tr> </tbody> </table>	09 67 002 9123 ³⁾	2.00 - 2.60 mm	09 67 002 9124	09 67 002 9125	09 67 002 9126	09 67 002 9129	1.20 - 2.00 mm	09 67 002 9130	09 67 002 9131	09 67 002 9132	09 67 002 9133	0.80 - 1.20 mm	09 67 002 9134	09 67 002 9135	09 67 002 9136											
Thread																																							
inner	outer																																						
4 - 40 UNC	4 - 40 UNC																																						
4 - 40 UNC	M3																																						
M3	4 - 40 UNC																																						
M3	M3																																						
09 67 002 9123 ³⁾	2.00 - 2.60 mm																																						
09 67 002 9124																																							
09 67 002 9125																																							
09 67 002 9126																																							
09 67 002 9129	1.20 - 2.00 mm																																						
09 67 002 9130																																							
09 67 002 9131																																							
09 67 002 9132																																							
09 67 002 9133	0.80 - 1.20 mm																																						
09 67 002 9134																																							
09 67 002 9135																																							
09 67 002 9136																																							
9 pole top entry hood for coding																																							
<p>Please insert digit for screw option</p> <p>Hexagonal screw, thread M3 with captive washer ▶ 1</p> <p>Hexagonal screw, thread 4-40 UNC with captive washer ▶ 2</p>	61 03 001 . 010 123																																						

1) MOQ = 50 pieces
 2) Stock items (standard versions) in bold type
 3) Standard versions